

For Use With Fire Extinguisher



1620 Series

Series 1620 and 1630 cabinets will accommodate a single portable Fire Extinguisher. Series 1640 will accommodate two portable Fire Extinguishers.

STANDARD EQUIPMENT

- * Heavy gauge steel construction tub, door and trim
- * White powder coat finish
- * Continuous steel piano hinge
- * Pull handle with roller catch

CABINET OPTIONS

- * Prefix **FR** for Fire Rated Cabinet
- * Suffix **AL** for clear anodized aluminum door and frame
- * Suffix **SS** for Stainless Steel # 4 finish door and frame
- * Suffix **FF** for Detention Grade Heavy Steel Door And Trim
- * Door Styles See page 2-5
- * Other cabinet options See page 2-7, 2-19 and 2-20

ORDERING PROCEDURE

- * Select cabinet Figure #
- * Select door style
- * Select Fire Extinguisher (Refer to 4000 Series)
- * Select cabinet options

Fig. No.	Trim Style	Trim Pro. Tp	Overall Inside box dimensions			Outside dim.		Wall Opening Required			FIRE RATED CABINETS Wall Opening Required FR Option			Extinguisher Capacity
			A	B	C	D	E	Width	Height	Depth	Width	Height	Depth	
1620	Recessed	3/8"	12	27	7 3/4	15 3/8	30 3/8	13	28	7 7/8	14	29 1/8	8 1/2	2 1/2,5,10,20lb. ABC Dry Chem.
1621	Semi-recessed	1 1/4"	12	27	7 3/4	15 3/8	30 3/8	13	28	6 3/4	14	29 1/8	7 3/8	2,2 1/2, 5 1/2,10 lb. BC 2 1/2 gal. W.P. 5,10,lb. CO2
1622		2 1/2"	12	27	7 3/4	15 3/8	30 3/8	13	28	5 1/2	14	29 1/8	6 3/8	
1624		4"	12	27	7 3/4	15 3/8	30 3/8	13	28	4	14	29 1/8	4 5/8	
1626	Trimless		12	27	7 3/4	12 1/4	27 1/4	12 1/2	27 1/2	8				5,10,lb. CO2
1628	Surface		15 3/16	30 3/16	8 1/4	15 3/8	30 3/8							2 1/2,5,11,15lb. Halotron
1630	Recessed	3/8"	16	32	7 3/4	19 3/8	35 3/8	17	33	7 7/8	18	34 1/8	8 1/2	2 1/2,5,10,20lb. ABC Dry Chem.
1631	Semi-recessed	1 1/4"	16	32	7 3/4	19 3/8	35 3/8	17	33	6 3/4	18	34 1/8	7 3/8	2,2 1/2, 5 1/2,10 lb. BC 2 1/2 gal. W.P. 5,10,15lb. CO2
1632		2 1/2"	16	32	7 3/4	19 3/8	35 3/8	17	33	5 1/2	18	34 1/8	6 3/8	
1634		4"	16	32	7 3/4	19 3/8	35 3/8	17	33	4	18	34 1/8	4 5/8	
1635	recessed	4 1/2"	16	32	7 3/4	19 3/8	35 3/8	17	33	3 1/2	18	34 1/8	4 1/8	5,10,15lb. CO2
1638	Surface		19 3/16	35 3/16	8 1/4	19 3/8	35 3/8							2 1/2,5,11,15lb. Halotron
1640	Recessed	5/16"	20	27	7 3/4	23 3/8	30 3/8	21	28	7 7/8	22	29 1/8	8 1/2	Two-Any Combination
1641	Semi-recessed	1 1/4"	20	27	7 3/4	23 3/8	30 3/8	21	28	6 3/4	22	29 1/8	7 3/8	2 1/2,5,10,20lb. ABC Dry Chem.
1642		2 1/2"	20	27	7 3/4	23 3/8	30 3/8	21	28	5 1/2	22	29 1/8	6 3/8	
1644	Semi-recessed	4"	20	27	7 3/4	23 3/8	30 3/8	21	28	4	22	29 1/8	4 5/8	2 1/2 gal. W.P. 5,10,lb. CO2
1645		4 1/2"	20	27	7 3/4	23 3/8	30 3/8	21	28	3 1/2	22	29 1/8	4 1/8	
1648	Surface		23 3/16	30 3/16	8 1/4	23 3/8	30 3/8							

Note: Add 5/8" to depth of wall opening required for cabinets with aluminum frame

